


Supplement

Title: 717 Inst.Sht. Supplement Issue: 4
Part Number: 690013 Issue Date: 8/17
Print Date: March 1998 Page Count: 4
Revision/Date: 2, 3/06

This supplement contains information necessary to ensure the accuracy of the document described above.

Change #1

On the second panel, under **Symbols**, add:

 N10140	Conforms to relative Australian standards
---	---

Change #2 59696, 480

On the first panel, under “The 717 Pressure Calibrators (hereafter, “the Calibrator”) include” add the following:

- 717 15G
- 717 10000G

On the second panel, under **Input Units**, add the following bullet and replace the paragraph under the bullets with:

- inH₂O @ 60 °F

If inappropriate units are selected, the pressure can be too low to be displayed or can cause the Calibrator to display **OL** (overload).

Under the **Replacement Parts and Accessories**, add the following to the Table:

Item	Parts or Accessory	Part Number	Qty
⑱	717 15G Top Case Decal	4058885	1
⑲	717 10000G Top Case Decal	4058897	1
⑳	717 15G LCD Bezel	4058851	1
㉑	717 10000G LCD Bezel	4058860	1

Under **Specifications** replace the entire section with:

Specifications


Specifications apply for ambient temperature from +18 °C to +28 °C unless stated otherwise. "Counts" are the number of increments or decrements of the least significant digit.

Model	Range	Max	Accuracy ^[1]	
			6 month	1 year
717 1G	-1 to 1 psi	5 psi	0.050 %	0.050 %
	-7 to 7 kPa	34.5 kPa		
717 15G	-12 to 15 psi	30 psi	0.025 %	0.035 %
	-83 to 103 kPa	207 kPa		
717 30G	-12 to 30 psi	60 psi	0.025 %	0.035 %
	-83 to 207 kPa	413 kPa		
717 100G	-12 to 100 psi	200 psi	0.025 %	0.035 %
	-83 to 690 kPa	1.4 mPa		
717 300G	-12 to 300 psi	375 PSI	0.035 %	0.050 %
	-83 to 2.1 mPa	2.6 mPa		
717 500G	0 to 500 psi	1000 psi	0.025 %	0.035 %
	0 to 3.4 mPa	6.9 mPa		
717 1000G	0 to 1000 psi	2000 psi	0.025 %	0.035 %
	0 to 6.9 mPa	13.8 mPa		
717 1500G	0 to 1500 psi	3000 PSI	0.025 %	0.035 %
	0 to 10.3 mPa	20.7 mPa		
717 3000G	0 to 3000 psi	6000 PSI	0.025 %	0.035 %

	0 to 20.7 mPa	41.4 mPa		
717 5000G	0 to 5000 psi	10000 PSI	0.025 %	0.035 %
	0 to 34.5 mPa	69 mPa		
717 10000G	0 to 10000 psi	15000 psi	0.035 %	0.050 %
	0 to 69 mPa	103.4 mPa		
[1] In an RF field of 1 V/m to 3 V/m, between the frequencies of 1.4 GHz to 2.0 GHz, add 120 counts to specified accuracy.				


Change #3, 59844

In the **Specification** section, add the following:

Specifications apply to the 717 Pressure Calibrators with firmware version 4.0 or greater. To verify the firmware version, push and hold  and power on the Calibrator.

Change #4, 67386

On the second panel, under **Symbols**, add:

	Conforms to relevant South Korean EMC Standards.
---	--

Under **General Specifications**, add:

Electromagnetic Compatibility (EMC)

International.....IEC 61326-1: Portable Electromagnetic Environment

CISPR 11: Group 1, Class A

Group 1: Equipment has intentionally generated and/or uses conductively-coupled radio frequency energy that is necessary for the internal function of the equipment itself.

Class A: Equipment is suitable for use in all establishments other than domestic and those directly connected to a low-voltage power supply network that supplies buildings used for domestic purposes. There may be potential difficulties in ensuring electromagnetic compatibility in other environments due to conducted and radiated disturbances.

Caution: This equipment is not intended for use in residential environments and may not provide adequate protection to radio reception in such environments.

Emissions that exceed the levels required by CISPR 11 can occur when the equipment is connected to a test object.

Korea (KCC).....Class A Equipment (Industrial Broadcasting & Communication Equipment)

Class A: Equipment meets requirements for industrial electromagnetic wave equipment and the seller or user should take notice of it. This equipment is intended for use in business environments and not to be used in homes.

USA (FCC)47 CFR 15 subpart B. This product is considered an exempt device per clause 15.103.